




NOTES:

1. EXIT BEAMS 1 & 2 PARALLEL AFTER BONDING TO < 2 ARCMIN
3. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: R(abs) < 0.25% @ 632.8nm
 - S2: EXTINCTION RATIO: $T_p/T_s > 1000:1$ @ 632.8nm
 - TRANSMITTANCE: $T_p > 95%$ @ 632.8nm
 - REFLECTION EFFICIENCY: $T_s > 99%$ @ 632.8nm
 - S3: NONE
4. RoHS COMPLIANT



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



REV. A	S1	S2	THIRD ANGLE PROJECTION		TITLE	10mm x 632.8mm, LATERAL DISPLACEMENT POLARIZING BEAMSPLITTER	
SURFACE QUALITY	40-20	40-20	ALL DIMS IN	mm	DWG NO	47190	SHEET 1 OF 1
SURFACE FLATNESS	$\lambda/8$	$\lambda/8$					