




NOTES:


1. SUBSTRATE: POLYMER FILM XP42-75
2. OPERATING TEMPERATURE: -40 TO +80 °C
3. WAVELENGTH RANGE: 400 - 700 nm
4. POLARIZATION: >99
5. TRANSMISSION (%):  
 Single: 42  
 Parallel: 36  
 Crossed: <0.004
6. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
 DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
 DO NOT MANUFACTURE  
 PARTS TO THIS DRAWING**

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

THIRD ANGLE PROJECTION 	TITLE		450.0 x 600.0mm, 0.75mm, POLARIZING LAMINATED FILM	
	ALL DIMS IN	mm	DWG NO	86192
				SHEET 1 OF 1