



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



COMPATIBLE TUBE LENS	Focal Length: 200mm
MAGNIFICATION	5X
MOUNTING THREAD	M26 x 36 TPI
NUMERICAL APERTURE NA	0.14
WORKING DISTANCE (mm)	34
MOUNTING THREADS	M26 x 36 TPI
FOCAL LENGTH FL (mm)	40
TYPE	Plan APO
FIELD OF VIEW, 1" SENSOR	2.56 x 1.92mm
FIELD OF VIEW, 1/2" SENSOR	1.28 x 0.96mm
FIELD OF VIEW, 2/3" SENSOR	1.76 x 1.32mm
FIELD OF VIEW, 24 DIAMETER FIELD EYEPIECE (mm)	4.8
DEPTH OF FOCUS (μm)	14
RESOLVING POWER (μm)	2
RoHS	NOT COMPLIANT

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® **Edmund Optics**®

THIRD ANGLE PROJECTION

TITLE

5X EO M Plan Apo Long Working Distance
Infinity Corrected

ALL DIMS IN

mm

DWG NO

59876

SHEET
1 OF 1