




NOTES:

1. COATING:
ALL SURFACES EXCEPT S1: Vacuum Black™
2. ABSORBANCE: 99.995% @ AOI > 60°
3. ABRASION RESISTANCE: High
4. HUMIDITY RESISTANCE: MIL-C-48497A
5. OPERATING TEMPERATURE(°C) : -50 to 150
6. WAVELENGTH RANGE: 0.3 - 5µm



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® Edmund Optics®

| | | | | |
|--|----|--------|-------------------------------------|-----------------|
| THIRD ANGLE PROJECTION  | | TITLE | 25mm Dia. Adhesive, Hexablack Panel | |
| ALL DIMS IN | mm | DWG NO | 37830 | SHEET 1 OF 1 |