




NOTES:

1. MAIN MATERIAL: BLACK ANODIZED ALUMINUM

2. MIN DIA: 10mm  
MAX DIA: 60mm

3. MAX EDGE THICKNESS: 4mm


4. RoHS: COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

**EO**® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	60mm, Bar-Type Lens/Filter Holder	
ALL DIMS IN	mm	DWG NO	55530	SHEET 1 OF 1