



NOTES:

- 1. SUBSTRATE: FUSED SILICA
- 2. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: 355nm HR Coating
 - R(ABS) > 99.8% @ 355nm @ 45° AOI
 - R(AVG) > 99.5% FROM 351-358nm @ 45° AOI
- DAMAGE THRESHOLD
 - PULSED: 6 J/cm² , 20ns, 20 Hz @ 355nm
 - CW: 1MW/cm² @ 355nm

3 FINE GRIND SURFACE

- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20-10	20-10
CLEAR APERTURE	25.45 x 18.00	Ø18.00
SURFACE FLATNESS	λ/20	λ/20
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION		Edmund Optics®	
ALL DIMS IN		TITLE	20mm, 1/20 WAVE, 355nm, HR CTD HYP, HT RA, FS PRISM
mm		DWG NO	37650
			SHEET 1 OF 1