


WHITE DIFFUSING GLASS

- Semi-Opaque White Glass
- Highly Diffusive to Create Even Illumination
- Diffusive on Both Surfaces




Transmission vs. Wavelength at Various Thicknesses

White Diffusing Glass has a thickness of 1.25mm. Other thicknesses shown are as a reference for Custom Products.



Relative Intensity vs. Angle for 405, 640, & 1064nm

Ideal diffusion is represented by the Cosine Function.



© COPYRIGHT 2018 EDMUND OPTICS, INC. ALL RIGHTS RESERVED