





FOCAL LENGTH (EFL): 200 ±2
BACK FOCAL LENGTH (BFL): 196,66

1 AR COATING: NONE

LEFT SURFACE			MATERIAL	RIGHT SURFACE	
R	103,36±0,103 CX		GLASS N-BK7 517/642	R	∞ PL
Øe	49			Øe	49
3/	3 (0,5) λ=632,8 nm			3/	3 (0,5) λ=632,8 nm
4/	-			4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)			5/	40 - 20 (MIL-PRF-13830B)
6/	-			6/	-
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®	
ROHS: COMPLIANT		SCALE: NONE			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				50,0mm Dia, x 200,0mm FL, Uncoated, Plano-Convex Lens	
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO
			45151		SHEET SIZE A4
					SHEET 1 OF 1