


LEFT SURFACE			MATERIAL		RIGHT SURFACE					
R	36,87±0,037 CX		GLASS	N-BK7 517/642	R	36,87±0,037 CX				
Øe	5,4				Øe	5,4				
3/	3 (0,5) λ=632,8 nm				3/	3 (0,5) λ=632,8 nm				
4/	-				4/	1,93'				
5/	40 - 20 (MIL-PRF-13830B)				5/	40 - 20 (MIL-PRF-13830B)				
6/	-				6/	-				
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		 Edmund Optics®					
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm								
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE					
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING					6mm Dia, x 36mm FL Uncoated, Double-Convex Lens					
INDICATIONS IN ACCORDANCE WITH ISO 10110					DWG NO					
			ALL DIMS IN:		mm		SHEET SIZE A4		SHEET 1 OF 1	