




FOCAL LENGTH (EFL): 4 ±0,04
BACK FOCAL LENGTH (BFL): 3,57

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	3,401±0,003 CX	GLASS N-LaSF9 850/322	R	∞ PL
Øe	2		Øe	2
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	52,94'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®				
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE 2,5mm Dia, x 4,0mm FL, Uncoated, Plano-Convex Lens				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			DWG NO 48643						
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING								SHEET SIZE A4	
INDICATIONS IN ACCORDANCE WITH ISO 10110			SHEET 1 OF 1						