


Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


400nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

450nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


500nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


550nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


600nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

650nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


700nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


750nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


800nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

850nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE

900nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


950nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

1000nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


1050nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

1100nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


1150nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

1200nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE

1250nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE

1300nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE

1350nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


1400nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

1450nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


1500nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

1550nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

1600nm Techspec Longpass Filter: OD >2.0 Coating Performance FOR REFERENCE ONLY

