NOTES:

MATERIAL

HOUSING: STAINLESS STEEL

LENS: D-ZK3

2. COATING


\$1 & \$2: R(ABS) < 1.0% @ 1050 - 1600nm


3. CLEA


CLEAR APERTURE: 5.50mm

4. ALIGNMENT WAVELENGTH: 1064nm

5. Rohs: Compliant







SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

THIRD ANGLE TITLE		TITLE	LightPath 354220 1064nm Alignment, 0.25 NA Fiber Collimator w/ FC/APC Connector	
ALL DIMS IN	mm	DWG NO	16707	SHEET 1 OF 1