




NOTES:
1. RoHS: COMPLIANT



2. DAMAGE THRESHOLD:
PULSED LIDT: $2.5 \text{ J/cm}^2 * (\tau/[\text{ns}])^{0.35}$
CW LIDT: 2.5 MW/cm^2

3. GROUP DELAY DISPERSION: 7690 fs^2



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	255mm, 515-540nm JENar™ F-Theta Scanning Lens
ALL DIMS IN	mm	DWG NO	16773
			SHEET 1 OF 1