




NOTES:
1. RoHS: COMPLIANT


2. GROUP DELAY DISPERSION: 759 fs²



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION 		TITLE	160mm, 900-1100nm JENar™ Silverline™ F-Theta Scanning Lens	
ALL DIMS IN	mm	DWG NO	17021	SHEET 1 OF 1