




NOTES:

- 1. RoHS: COMPLIANT
- 2. GROUP DELAY DISPERSION: 904 fs<sup>2</sup>



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
 DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
 DO NOT MANUFACTURE  
 PARTS TO THIS DRAWING**



THIRD ANGLE PROJECTION		TITLE	255mm, 900-1100nm JENar™ Silverline™ F-Theta Scanning Lens	
ALL DIMS IN	mm	DWG NO	17022	SHEET 1 OF 1