




- NOTES:
- 1. SUBSTRATE:
TAC FILM
 - 2. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: NONE
 - 3. PROTECTIVE FILM ON NON-MATTE SURFACE SHOULD BE REMOVED BEFORE USE
 - 4. WAVELENGTH RANGE: 300 - 1100 nm
 - 5. ROHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

THIRD ANGLE PROJECTION 		 Edmund Optics®	
TITLE		100 x 100mm Light Diffusing Film	
ALL DIMS IN	mm	DWG NO	SHEET
		17683	1 OF 1