NOTES:


1. SUBSTRATE:


FUSED SILICA (CORNING 7980)

- 2. S2 TO BE PARALLEL WITH S1 TO WITHIN <1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(AVG) ≤0.5% @ 600 - 1050nm

4. FINE GRIND SURFACE

## 5. ROHS COMPLIANT





## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

	\$1	\$2	]			Edmund Optic	S®
SHAPE	PLANO	PLANO			TITLE	20mm Dia., 2mm Thick, NIR I Coated, λ/4 Fused Silica Window	
SURFACE QUALITY	40-20	40-20					
CLEAR APERTURE (mm)	Ø18.00	Ø18.00					CULLET
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	18339	SHEET 1 OF 1