

NOTES:


- 1. SUBSTRATE MATERIAL: Fused Silica
- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO 30 arcsec
- 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: SILVER WITH MULTILAYER OVERCOAT
R{avg}>99% @ 850-1150 nm, 0 deg AOI, Rs>99% @ 800-1150 nm, 45 deg AOI, Rp> 98.5 % @ ~850 – 1100 nm, 45 deg AOI

S2: NONE


4. FINE GRIND SURFACE

5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	<div>THIRD ANGLE PROJECTION</div> 		TITLE	MIRROR 1/10 WAVE UF SILVER 800-1150NM 10mm DIA			
SURFACE QUALITY	20 - 10	COMMERCIAL POLISH							
SURFACE FLATNESS	$\lambda/10$	N/A	<div>ALL DIMS IN</div> <div>mm</div>		DWG NO	22009			SHEET 4 OF 20
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED							