




MOUNTING SLOTS COMPATIBLE WITH
BREADBOARDS WITH 50mm OR 2in
HOLE SPACING



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE
PROJECTION

TITLE

430nm, 1.5mW, 500mA, SMA Connector,
Fiber-Coupled LED

ALL DIMS IN

mm

DWG NO

23729

SHEET
3 OF 18