




MOUNTING SLOTS COMPATIBLE WITH
BREADBOARDS WITH 50mm OR 2in
HOLE SPACING



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Optics®

THIRD ANGLE
PROJECTION

TITLE

565nm, 5mW, 1000mA, SMA Connector,
Fiber-Coupled LED

ALL DIMS IN

mm

DWG NO

23734

SHEET
8 OF 18