




MOUNTING SLOTS COMPATIBLE WITH
BREADBOARDS WITH 50mm OR 2in
HOLE SPACING



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION		TITLE	808nm, 5mW, 500mA, SMA Connector, Fiber-Coupled LED	
ALL DIMS IN	mm	DWG NO	23740	SHEET 14 OF 18