




MOUNTING SLOTS COMPATIBLE WITH
BREADBOARDS WITH 50mm OR 2in
HOLE SPACING



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION	TITLE	850nm, 8mW, 1500mA, SMA Connector, Fiber-Coupled LED	
ALL DIMS IN	mm	DWG NO	SHEET 15 OF 18
		23741	