




MOUNTING SLOTS COMPATIBLE WITH  
BREADBOARDS WITH 50mm OR 2in  
HOLE SPACING



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® Edmund Optics®

THIRD ANGLE PROJECTION	TITLE	1050nm, 4mW, 600mA, SMA Connector, Fiber-Coupled LED	
ALL DIMS IN	mm	DWG NO	SHEET 18 OF 18
		23744	