





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
SHAPE	PLANO
$\Delta\lambda$ t	<35
TH (%)	>85
CUT-OFF POSITION $\lambda_c$ (nm)	370±6
SURFACE QUALITY	60-40
WAVELENGTH	UV
BEVEL	PROTECTIVE AS NEEDED



TITLE	Ø50mm, HOYA L-37 LONGPASS FILTER		
DWG NO	66075	SHEET 1 OF 1	

ALL DIMS IN

mm