

[See all 75 Products in Family](#)

# LightPath 354280 | 6.5mm Dia., 0.15 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-113** **8 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ €85<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	€85,00 each
Qty 11-49	€76,50 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

### General

Thickness: 0.25 (t) (mm)  
Material: BK7

Compatible Window:

354280

Lightpath Lens Code:

Aspheric Lens

Type:

Typical Applications:  
Collimate or Focus Laser Light

## Physical & Mechanical Properties

Diameter (mm):  
6.50 ±0.020

Clear Aperture CA (mm):  
5.5

Edge Thickness ET (mm):  
1.78

Center Thickness CT (mm):  
2.18 ±0.05

Bevel:  
Protective as needed

Distance from Window to Lens (D) (mm):  
15.856

## Optical Properties

Effective Focal Length EFL (mm):  
18.40 @ 780nm

Numerical Aperture NA:  
0.15

Substrate:   
[D-ZK3](#)

Focal Length Tolerance (%):  
±1

Aspheric Design Wavelength (nm):  
780

Coating:  
BBAR (350-700nm)

Coating Specification:  
R<sub>avg</sub> ≤0.5% @ 350 - 700nm

Surface Quality:  
40-20

f#:  
3.33

Abbe Number (v<sub>d</sub>):  
60.88

Index of Refraction (n<sub>d</sub>):  
1.586

Wavelength Range (nm):  
350 - 700

Working Distance (mm):  
17.11

Conjugate Distance:  
Infinite

Focal Length Specification Wavelength (nm):  
780.00

Transmitted Wavefront Error (λ, RMS):  
< 0.09

## Material Properties

Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):  
7.6

## Environmental & Durability Factors

Operating Temperature (°C):  
≤200

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Reach 247:  
[Compliant](#)

## Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam

shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



## Technical Information



## Compatible Mounts