

TECHSPEC[®] 0.15X - 0.5X M Series Non-Telecentric Lens



Stock **#87-536** 20+ In Stock

-

1

+

€650⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€650,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Variable Magnification Lens	Type:
Non-Telecentric, Variable Magnification	Style:

Physical & Mechanical Properties

Variable	Iris Option:
----------	--------------

59.20	Length (mm):
32	Maximum Diameter (mm):
101	Weight (g):

1.92	Maximum Rear Protrusion (mm):
------	-------------------------------

Optical Properties

Field of View at Max Sensor Format: Horizontal: 61.6 - 17.6mm - 15.8° Vertical: 61.6 - 13.2mm - 11.8° Diagonal: 46.9 - 22.0mm - 19.8°	
75 lp/mm @ >20%	Resolution:

11.00	Maximum Image Circle (mm):
0.0587	Numerical Aperture NA, Object Side:

5 (4)	Number of Elements (Groups):
<0.1	Typical Distortion @ 588nm (%):

0.15X- 0.5X	Primary Magnification PMAG:
50 - 179.8	Working Distance (mm):

58.7 x 44.0 - 17.6 x 13.2	FOV @ Max Sensor Format, H x V (mm):
f/2.8 - f/22	Aperture (f/#):

λ/4 MgF ₂ @ 550nm	Coating Specification:
30.1	Entrance Pupil Position (mm):

28.92	Object Space Principal Plane (mm):
-16.17	Image Space Principal Plane (mm):

0.05	Maximum Distortion (%):
-15.04	Exit Pupil Position (mm):

VIS	Lens Wavelength Range:
-----	------------------------

Sensor

2/3"	Maximum Sensor Format:
------	------------------------

Threading & Mounting

M25.5 x 0.50 (Female)	Filter Thread:
C-Mount	Mount:

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	REACH 201:
View	Certificate of Conformance:

Product Details

- Variable Magnication Lens
- Up to 5 MegaPixels, 3.45m Pixel Size Sensors
- ⅔", C-Mount Lens

TECHSPEC® M Series Variable Magnification Lenses are designed for applications that may require constant adjustment of a system's field of view. Each lens provides a range of magnications that users can adjust or lock down with a set screw. With coverage for up to ⅔" format sensors, these lenses feature compact, C-mount compatible designs for easy system integration. TECHSPEC® M Series Variable Magnification Lenses also include an adjustable iris to control light throughput and improve image quality. These lenses are ideal for use in high magnication machine vision and factory automation.

Note: Customized magnication versions are also available to meet volume requirements. Please contact technical support to discuss your specific requirements.

