

0.19 - 20 μ m, 3.8J, Pyroelectric Energy Detector



0.19 - 20 μ m, 3.8J, Pyroelectric Energy Detector

Stock #78-468 **NEW** 1 In Stock

⊖ 1 ⊕ €2.610⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	€2.610,00 each
Qty 5+	€2.350,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Maximum Incident Energy Density (J/cm², 10ns Pulses):

0.6

General

QE25LP-S-MB-INT-D0 **Model Number:**

Convection **Cooling Method:**

Note:

1 of (#15-267) is included

3.8 **Maximum Incident Energy (J):**

Integra (Integrated) **Compatible Meters:**

Physical & Mechanical Properties

50 x 50 x 14 **Dimensions (mm):**

120 **Weight (g):**

0.12 **Weight (kg):**

25 x 25 **Active Area (mm):**

Optical Properties

190 - 20000 **Wavelength Range (nm):**

0.19 - 20 **Wavelength Range (µm):**

Sensor

Pyroelectric **Type of Sensor:**

Electrical

5,000 **Maximum Incident Beam Power (mW):**

5 **Maximum Incident Beam Power (W):**

4 µJ **Noise Level:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Photodetectors, Thermopiles, and Pyroelectric Detectors Available
- Various Active Area Sizes Across a Wide Range of Sensitivities
- [Meterless](#) and [Wireless](#) Detectors Also Available

Gentec-EO Integra USB Power and Energy Detectors combine a power meter and detector in one convenient package while providing fast response times and accurate measurements for beam analysis. These detectors are designed with a USB connector for easy connection to a PC or other acquisition system and include user-friendly software allowing for control via PC or serial commands. Versatile pyroelectric energy detectors with broadband coatings are optimized for low to high power densities. Gentec-EO Integra USB Power and Energy Detectors can be used with a variety of laser powers ranging from the nanowatts to multi-kilowatts. These detectors are ideal for laser energy measurement, thermal imaging, and remote sensing applications.