

[See all 14 Products in Family](#)

LightPath 354061 | 6.33mm Dia., 0.24 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock #83-702 **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ €85⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	€85,00 each
Qty 11-49	€76,50 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

354061 **Lightpath Lens Code:**

Aspheric Lens **Type:**

Physical & Mechanical Properties

Diameter (mm):

6.33 ±0.015

Clear Aperture CA (mm):

5.20

Edge Thickness ET (mm):

1.64

Center Thickness CT (mm):

2.43 ±0.05

Bevel:

Protective as needed

Optical Properties

Effective Focal Length EFL (mm):

11.00 @633nm

Numerical Aperture NA:

0.24

Substrate:

[D-ZK3](#)

Focal Length Tolerance (%):

±1

Aspheric Design Wavelength (nm):

633

Coating:

BBAR (600-1050nm)

Coating Specification:

R_{abs} <1.0% @600 - 1050nm

Surface Quality:

60-40

f#:

2.08

Abbe Number (v_d):

61.16

Index of Refraction (n_d):

1.589

Wavelength Range (nm):

600 - 1050

Working Distance (mm):

9.600

Conjugate Distance:

Infinite

Focal Length Specification Wavelength (nm):

633.00

Transmitted Wavefront Error (λ, RMS):

<0.178

Material Properties

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

7.6

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Compliant](#)

Product Details

- Compact, Molded Aspheric Lens Design
- Improved Performance Compared to Doublet and Triplet Lenses
- Ideal for Laser Tools and Measurement Systems

LightPath® Laser Tool Molded Aspheric Lenses are designed to fulfill the needs of a variety of tools and measurement systems utilizing laser diodes, including leveling lasers, projectors, scanners, trackers, and gun sights. By utilizing a single aspheric lens, the need for a multi-lens system is eliminated, allowing for a more compact and robust design. Each aspheric lens is offered with various anti-reflection coatings for optimum transmission in the visible and NIR wavelength ranges. LightPath® Laser Tool Molded Aspheric Lenses' anti-reflection coating options for each lens provides <1% average reflection over the entire design wavelength range. The lenses are offered in four different diameters: 3mm, 4.70mm, 6mm, and 6.33mm.

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)