

TECHSPEC® 0.28X, 28.7mm F-Mount PlatinumTL™ Telecentric Lens



0.28X Magnification

Stock #62-922 20+ In Stock

-

1

+

€5.560⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€5.560,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Series:

PlatinumTL™ Series

Stock No. of Mounting Clamp:

#63-440 Sold Separately

Type:

Telecentric Lens

Physical & Mechanical Properties

Iris Option:

Variable	
167.60	Length (mm):
138.6	Maximum Diameter (mm):
736	Weight (g):
46.5	Flange Distance (mm):

Optical Properties

80.0mm	Horizontal Field of View, APS-C Sensor:
102.5mm	Field of View, 28.7mm Sensor:
61.8mm	Horizontal Field of View, 4/3" Sensor:
50.7mm	Horizontal Field of View, 1.1" Sensor:
45.7mm	Horizontal Field of View, 1" Sensor:
31.8mm	Horizontal Field of View, 2/3" Sensor:
22.9mm	Horizontal Field of View, 1/2" Sensor:
28.70	Maximum Image Circle (mm):
0.023	Numerical Aperture NA, Object Side:
10 (7)	Number of Elements (Groups):
<0.035	Typical Telecentricity @ 588nm (°):
<0.012	Typical Distortion @ 588nm (%):
0.28X	Primary Magnification PMAG:
0.28	Telecentric Lens Magnification:
182.00	Working Distance (mm):
80.0 x 60.0	FOV @ Max Sensor Format, H x V (mm):
f/6 - f/22	Aperture (f/#):
425 - 675nm BBAR	Coating:
±6.9 at f/10 (20% @ 20 lp/mm)	Depth of Field (mm):
0.28X	Magnification:
VIS	Lens Wavelength Range:

Sensor

APS-C	Maximum Sensor Format:
2.74	Pixel Size (µm):

Threading & Mounting

M132 x 0.75 (Female)	Filter Thread:
F-Mount	Mount:

Regulatory Compliance


View	Certificate of Conformance:
----------------------	-----------------------------

Product Details


- High Resolution f/6 Bi-Telecentric Lens for Measurement
- Up to 35 MegaPixels, 2.8µm Pixel Size Sensors
- APS-C, C-Mount, T-Mount, F-Mount Telecentric Lens
- Magnification from 0.28X to 1.7X

TECHSPEC® PlatinumTL™ Telecentric Lenses are designed for semiconductor and electronics inspection, measurement, and gauging applications. The precision designs feature high telecentricity (<0.1°), low distortion (<0.1%), and high light throughput with an adjustable aperture that achieves f/6 when fully open. Capable of supporting large format 28.7mm diagonal sensors, these lenses are compatible with the Sony IMX342 APS-C sensor and other similar format sensors such as the Sony IMX530. TECHSPEC® PlatinumTL™ Telecentric Lenses produce unparalleled levels of contrast yielding maximum image quality with the highest degree of measurement accuracy. These lenses are suitable for high vibration environments and feature a removable recessed set screw for securing the iris in place.

Technical Information




#62-922, 0.28X, 28.7mm F-Mount PlatinumTL™ Telecentric Lens, Distortion Plot




#62-922, 0.28X, 28.7mm F-Mount PlatinumTL™ Telecentric Lens, Relative Illumination Plot



#62-922, 0.28X, 28.7mm F-Mount PlatinumTL™ Telecentric Lens, Telecentricity Plot



#62-922, 0.28X, 28.7mm F-Mount PlatinumTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 182mm Working Distance, f6



Modulation Transfer Function: 62-922, .28X

Contrast (%)

Spatial Frequency (LP/mm)

Fields

- Diff. Limit
- 32,6.00mm
- 32,6.80mm
- 32,13.5mm

Working Distance: 182.00mm F/Number: f/10.00 Wavelength Range: 486nm-656nm

Depth of Field: 62-922, .28X

Contrast (%)

WD Change From 182mm (mm)

Fields

- TS, 5.00mm
- TS, 8.00mm
- TS, 13.95mm

Working Distance: 182.00mm F/Number: f/10.00 Wavelength Range: 486nm-656nm

Description		Stock No.	Flange	Length (A)	Front Diameter (B)	Back Diameter (C)
0.28X	C-Mount	#62-933	17.5mm	230.8mm	60.5mm	33.5mm
0.5X	C-Mount	#62-932	17.5mm	174.9mm	50mm	33.5mm
1.7X	C-Mount	#63-232	17.5mm	189.5mm	60mm	46mm
0.28X	F-Mount	#62-922	46.5mm	167.6mm	138.6mm	55mm
	M42 x 1.0	#62-923	6.56mm	208.5mm	138.6mm	50mm
	M42 x 1.0	#62-924	19.53mm	195.5mm	138.6mm	50mm
0.5X	F-Mount	#62-912	46.5mm	143mm	90mm	55mm
	M42 x 1.0	#62-913	6.56mm	184mm	90mm	50mm
	M42 x 1.0	#62-914	19.53mm	171.1mm	90mm	50mm
0.9X	F-Mount	#62-902	46.5mm	170.8mm	65mm	55mm
	M42 x 1.0	#62-903	6.56mm	210.7mm	65mm	53mm
	M42 x 1.0	#62-904	19.53mm	197.8mm	65mm	53mm

Technical drawing of a camera lens showing dimensions A, B, and C. Dimension A is the total length of the lens. Dimension B is the front diameter of the lens. Dimension C is the back diameter of the lens.