

0.28X Mag, InfiniGage CW Precision Spacer

See More by [Infinity Photo-Optical Company](#)



Stock #64-870 [CONTACT US](#)

⊖ 1 ⊕ €78⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | €78,00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Lens Accessory **Type:**
Compatible Lens:
[#64-877](#)

Optical Properties

Horizontal Field of View, 1/2" Sensor:
22.9mm
Horizontal Field of View, 1/3" Sensor:

17.1mm

95.00 **Working Distance (mm):**

0.28X **Magnification:**

Threading & Mounting

C-Mount **Mount:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **Reach 224:**

[View](#) **Certificate of Conformance:**

Product Details

- Accurate Measurements Based on Field of View
- 7 Spacer Options for a Wide Range of Magnifications
- UV Option Available

The InfiniGage™ main lens mates with seven precision spacers for multiple magnification and working distance choices. Simply set InfiniGage™ to the desired magnification and begin making accurate measurements. The InfiniGage™ accepts 11.8mm to 12.5mm diameter filters for polarization or color analysis without changing outer dimensions. The InfiniGage™ can be doubled in magnification by simply adding a DL Doubler Tube, reducing the FOV by a factor of two. The InfiniGage™ is also available in UV which is optimized for best performance from 250nm-700nm.

Note: InfiniGage™ CW option is only compatible with CW Precision Spacers.

Technical Information

| | Magnification | Working Distance | Field of View on 1/2" Sensor | Field of View on 1/3" Sensor |
|--|---------------|------------------|------------------------------|------------------------------|
| InfiniGage Precision Spacer with 2X Amplifier (Optional) | 0.25X | 286mm | 25.6mm | 19.2mm |
| | 0.5X | 155mm | 12.8mm | 9.6mm |
| | 0.66X | 120mm | 9.7mm | 7.3mm |
| | 1.0X | 85mm | 6.4mm | 4.8mm |
| | 1.3X | 72mm | 4.9mm | 3.6mm |
| | 1.5X | 67mm | 4.3mm | 3.2mm |
| | 2.0X | 52mm | 3.2mm | 2.4mm |