

[See all 74 Products in Family](#)

# LightPath 355375 | 6.51mm Dia., 0.30 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-130** [CONTACT US](#)

[Other Coating Options](#)

⊖ 1 ⊕ €75<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	€75,00 each
Qty 11-49	€67,50 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

### General

Thickness: 0.250 (t) (mm)  
Material: BK7

**Compatible Window:**

355375

**Lightpath Lens Code:**

Aspheric Lens

**Type:**

Typical Applications:  
Collimate or Focus Laser Light

## Physical & Mechanical Properties

Diameter (mm):  
6.51 ±0.020

Clear Aperture CA (mm):  
4.54

Edge Thickness ET (mm):  
2.71

Center Thickness CT (mm):  
3.19 ±0.04

Bevel:  
Protective as needed

Distance from Window to Lens (D) (mm):  
5.151

## Optical Properties

Effective Focal Length EFL (mm):  
7.50 @ 780nm

Numerical Aperture NA:  
0.30

Substrate:   
[D-ZLaF52LA](#)

Focal Length Tolerance (%):  
±1

Aspheric Design Wavelength (nm):  
780

Coating:  
BBAR (600-1050nm)

Coating Specification:  
R<sub>abs</sub> <1.0% @ 600 - 1050nm

Surface Quality:  
40-20

f#:  
1.67

Abbe Number (v<sub>d</sub>):  
40.79

Index of Refraction (n<sub>d</sub>):  
1.806

Wavelength Range (nm):  
600 - 1050

Working Distance (mm):  
5.8

Conjugate Distance:  
Infinite

Focal Length Specification Wavelength (nm):  
780.00

Transmitted Wavefront Error (λ, RMS):  
< 0.05

## Material Properties

Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):  
6.9

## Environmental & Durability Factors

Operating Temperature (°C):  
≤200

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)


Certificate of Conformance:  
[View](#)

Reach 247:  
[Compliant](#)

## Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



## Technical Information

