

[See all 74 Products in Family](#)

# LightPath 354125 | 11mm Dia., 0.50 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#33-426** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ €119.<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | €119,00 each                  |
| Qty 11-49      | €107,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

### General

Thickness: 0.25 (t) (mm)  
Material: B-K7

**Compatible Window:**

354125

**Lightpath Lens Code:**

Aspheric Lens

**Type:**

Typical Applications:  
Collimate or Focus Laser Light

## Physical & Mechanical Properties

Diameter (mm):  
11.00 ±0.015

Clear Aperture CA (mm):  
10

Edge Thickness ET (mm):  
1.092

Center Thickness CT (mm):  
3.64 ±0.40

Bevel:  
Protective as needed

## Optical Properties

Effective Focal Length EFL (mm):  
10.00 @ 633nm

Numerical Aperture NA:  
0.50

Substrate:   
[D-ZK3](#)

Focal Length Tolerance (%):  
±1

Aspheric Design Wavelength (nm):  
633

Coating:  
BBAR (600-1050nm)

Coating Specification:  
R<sub>abs</sub> <1.0% @ 600 - 1050nm

Surface Quality:  
60-40

f#:  
1.00

Abbe Number (v<sub>d</sub>):  
60.88

Index of Refraction (n<sub>d</sub>):  
1.586

Wavelength Range (nm):  
600 - 1050

Working Distance (mm):  
7.8

Conjugate Distance:  
Infinite

Focal Length Specification Wavelength (nm):  
633.00

Transmitted Wavefront Error (λ, RMS):  
< 0.09

## Material Properties

Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):  
7.6

## Environmental & Durability Factors

Operating Temperature (°C):  
≤200

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Reach 247:  
[Compliant](#)

## Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.

## Technical Information

