

[See all 13 Products in Family](#)

Coherent® Micro VLM™ Laser Diode 0220-970-00 | 0.95mW 670nm

See More by [Coherent®](#)



Coherent® Micro VLM™ Laser Diode

Stock **#52-263** 10 In Stock

-

1

+

€156^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€156,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



General

Type:	
Micro VLM	
Drive Circuitry:	
Fully Shielded, Reverse Polarity Protected	
Type of Laser:	
Diode	

II		Laser Class - CDRH:
Standard 9 V Battery: 5		Operating Lifetime (hours):
Physical & Mechanical Properties		
+0/ - 0.0762	Housing Tolerance (mm):	
15.00	Pointing Accuracy (arcmin):	
0.375		Diameter (inches):
0.73		Length (inches):
Optical Properties		
670.00		Wavelength (nm):
±10		Wavelength Tolerance (nm):
0.2 - 0.3		Wavelength Stability (nm/°C):
<10		Beam Astigmatism (µm):
4 x 1		Beam Diameter (mm):
0.3 x 1.2		Beam Divergence (mrad):
Red		Color:
Electrical		
0.95 (Maximum)		Output Power (mW):
±4		Output Power Tolerance (%):
MIL Spec. Std. 1686B, Class 2		ESD Protection:
70.00		Current (mA):
Hardware & Interface Connectivity		
Power Supply Required and Sold Separately. USA: #59-099 Europe: #35-201 Japan: #59-099 Korea: #33-771 China: #59-099		Power Supply:
3 - 6 VDC		Power Requirement:
36" Length, Red (+), Black (-), Case (+)		Electrical Leads/ Pin Connections:
Free Space		Output Type:
Environmental & Durability Factors		
-10 to +40		Operating Temperature (°C):
-40 to +80		Storage Temperature (°C):
Regulatory Compliance		
Exempt		RoHS 2015:
Contains SVHC(s)		Reach 224:
View		Certificate of Conformance:

Product Details



- Robust, High Quality Laser Diodes with Small Form Factor
- 635nm and 670nm High Visibility Wavelengths
- Sophisticated Electronic Design for Consistent Beam Properties

Coherent® Visible Laser Diode Modules feature a compact form factor to help users achieve space saving designs in systems that require a collimated light source. The simple design of these laser diodes allows for quick and

efficient incorporation into a wide array of optical systems. Asophisticated electronic design aids in producing consistent laser power and beams. Coherent® Visible Laser Diode Modules with advanced AlignLock™ optical assembly technology provide a remarkable beam-pointing alignment of <4.3mrad, making these laser diodes a great choice for precision applications. These robust, compact laser diodes are typically used in machine vision, medical equipment, and many other industrial applications.

Note: [Power Supply](#), sold separately, is required for operation.

Technical Information



VLM™ High Quality Laser Diode Module - Micro Series