


**TECHSPEC® 0° AOI, 20.0mm Square, Cold Mirror**



TECHSPEC High Performance Cold Mirrors

Stock #64-436 **4 In Stock**

⊖ 1 ⊕ €54.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	€54,00 each
Qty 10-25	€48,50 each
Qty 26-49	€46,25 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Cold Mirror **Type:**

**Physical & Mechanical Properties**

1.10 ±0.2 **Thickness (mm):**

**Dimensions (mm):**

20.0 x 20.0

**Dimensional Tolerance (mm):**

+0.0/-0.2

**Length (mm):**

20.00

**Width (mm):**

20.00

## Optical Properties

**Transmission (%):**

Longpass Filter

**Coating Type:**

Dielectric

**Coating:**

Cold Mirror, 0°

**Surface Flatness (P-V):**

4 - 6λ

**Wavelength Range (nm):**

400 - 1150

**Substrate:**

BOROFLOAT®

**Angle of Incidence (°):**

0

**Coating Specification:**

R<sub>avg</sub> ≥ 95% @ 400 - 690nm and T<sub>avg</sub> ≥ 90% @ 750 - 1200nm  
AR Coating: R<sub>avg</sub> < 1% @ 700 - 1150nm

**Surface Quality:**

80-50

## Regulatory Compliance

**RoHS 2015:**

Compliant

**Certificate of Conformance:**

[View](#)

**Reach 247:**



Compliant

## Product Details

- >95% Reflection from 400 - 690nm
- >90% Transmission from 750 - 1200nm
- Optimized for 0° or 45° Angle of Incidence

TECHSPEC® High Performance Cold Mirrors feature a multi-layer dielectric coating optimized for greater than 95% reflection of visible light and greater than 90% transmission of IR wavelengths. Cold mirrors are designed for use in any application where heat build-up can cause damage or adverse effects. For high power illumination, forced air cooling is recommended.

## Technical Information



**Quote Your Size**

## Compatible Mounts

---