


TECHSPEC® 10mm Dia Protected Silver,  $\lambda/20$  Mirror



Stock **#34-386** 16 In Stock

-

1

+

€166<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €166,00 each                  |
| Qty 6-25       | €132,00 each                  |
| Qty 26-49      | €125,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Flat MirrorType:

Physical & Mechanical Properties

10.00 +0.0/-0.20Diameter (mm):

2.00 ±0.20Thickness (mm):

Commercial Polish

Back Surface:

90.00

Clear Aperture (%):

Ground, protective bevel as needed

Edges:

30.00

Parallelism (arcsec):

Optical Properties

Metal

Coating Type:

Protected Silver (450-10000nm)

Coating:

λ/20 (flatness pre-coating)

Surface Flatness (P-V):

450 - 10000

Wavelength Range (nm):

Fused Silica (Corning 7980)

Substrate: ☐

R<sub>avg</sub> >98% @450 - 2000nm  
R<sub>avg</sub> >98% @2000 - 10,000nm

Coating Specification:

20-10

Surface Quality:

Regulatory Compliance

Compliant

RoHS 2015:

View

Certificate of Conformance:

Compliant

Reach 247:


Product Details

- Precision Fused Silica Substrate
- 20-10 Surface Quality
- Low Coefficient of Thermal Expansion

TECHSPEC® λ/20 First Surface Mirrors are polished to industry leading surface accuracy and quality specifications to minimize reflected wavefront error. These mirrors feature a precision fused silica substrate with a low coefficient of thermal expansion. Multiple coating options are available, allowing these mirrors to be integrated into applications spanning the visible through infrared spectra. TECHSPEC® λ/20 First Surface Mirrors are ideal for beam steering and reflection applications and are available in a variety of size, thickness, and coating options.

**Note:** Surface flatness is measured before coating.

Technical Information



Coating Curves

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

;