

[See all 1 Products in Family](#)

1/2" CCD NIR (1460-1600nm) Analog Camera, CCIR



1460-1600nm Near-Infrared Camera (Front)



Stock #56-848 **1 In Stock**

⊖ 1 ⊕ €3.050⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€3.050,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

NIR

Spectrum:

General

NIR Camera

Type:

Scintacor

Manufacturer:

Physical & Mechanical Properties

64.6 x 34 x 37
Dimensions (mm):

90.00
Weight (g):

Full
Housing:

Sensor

1/2"
Sensor Format:

0.40
Resolution (Megapixels):

752 x 582
Pixels (H x V):

8.6 x 8.3
Pixel Size, H x V (µm):

6.4 x 4.8
Sensing Area, H x V (mm):

Interlaced CCD
Type of Sensor:

1/60 - 1/100,000s
Exposure Time:

CCIR
Signal Format:

Hardware & Interface Connectivity

Analog
Interface:

BNC
Connector:

220 V, 50 Hz Included
Power Supply:

Internal
Synchronization:

12 VDC, 160 mA
Power Requirement:

Threading & Mounting

C-Mount
Mount:

1/4-20 TPI Tapped
Mounting Threads:

Environmental & Durability Factors

-10 to 40
Operating Temperature (°C):

Regulatory Compliance

[View](#)
Certificate of Conformance:

Product Details

- Low Cost
- Compact Size
- Standard Analog Video Output
- High Speed Electronic Shutter

This near IR camera utilizes a high resolution CCD array that has been specially treated with a phosphor coating. The result is a camera that has an effective response between 1460nm to 1600nm at a cost much lower than seen with other detector technologies. The high-speed electronic shutter allows for easy attenuation of high-level signals often associated with laser applications. Features a maximum CW power saturation of 100mW/cm² at 1550nm. The camera is ideal for applications including laser alignment, telecommunication testing, as well as inspection. While standard CCD lenses can be utilized in the near IR, their optical designs and coating are generally not optimized for this region of the spectrum. We recommend video lenses designed specifically for the near IR region.