

[See all 33 Products in Family](#)

## 20 x 20mm, 800µm Pitch, 1.7° Divergence, Double Sided Cyl. Lens Array



Stock **#23-874** **3 In Stock**

- 1 + €676<sup>.00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-10	€676,00 each
Qty 11-25	€591,00 each
Qty 26-49	€557,00 each
Need More?	<a href="#">Request Quote</a>

! Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Lens Array **Type:**

### Physical & Mechanical Properties

20.0 x 20.0 ± 0.10 **Dimensions (mm):**

11.100 **Radius R (mm):**

2.00 ±0.1 **Thickness (mm):**

## Optical Properties

24.70 @ 1064nm **Effective Focal Length EFL (mm):**

**Fused Silica** (Corning 7980) **Substrate:**

Uncoated **Coating:**

200 - 2200 **Wavelength Range (nm):**

1.7 (Full Width) **Divergence Angle (°):**

800 **Pitch (µm):**

Double-Sided (with cross-oriented lenses) **Array Type:**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **Reach 250:**

## Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.