

120 MHz Fiber Coupled Optical Receiver Module



Stock #87-324 CLEARANCE **5 In Stock**

- 1 + €187⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€187,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Optical Properties

1310 - 1550 **Wavelength Range (nm):**

50/125/245/900 **Fiber Diameter (µm):**

Sensor

25.00 **Dynamic Range (dB):**

Electrical

Hardware & Interface Connectivity

FC/PC **Connector:**

Regulatory Compliance


[View](#) **Certificate of Conformance:**

Product Details

- High Sensitivity and Overload Power with Wide Dynamic Range
- Designed for Bandwidths of 3MHz and 120MHz and Wavelength Ranges of 1310 – 1550nm
- Ideal for Biomedical, Industrial, or Telecommunication Optical Sensor Systems

Fiber-Coupled Optical Receiver Modules are ideal for use in biomedical optical sensor systems or for industrial and telecommunication sensing applications. Fiber-Coupled Optical Receiver Modules feature high sensitivity and high overload power, in addition to wide dynamic ranges. These receiver modules are designed for use in common telecommunication wavelength ranges.

Technical Information



Pin	Function
1	-5V detector bias
2, 6, 9, 11	No connection
12, 13, 14	No connection
3, 5, 8	Ground
4	-5V (LDFR = NC)
7	Output
10	+5V