

**TECHSPEC® 12.5mm Dia. 400 - 750nm Broadband  $\lambda/4$  Mirror**



Broadband Dielectric  $\lambda/4$  Mirrors

Stock **#70-667** **7 In Stock**

⊖ 1 ⊕ €69.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€69,50 each
Qty 6-25	€55,50 each
Qty 26-49	€52,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Flat Mirror **Type:**

**Physical & Mechanical Properties**

12.50 +0.00/-0.25 **Diameter (mm):**

**Thickness (mm):**

2.00 ±0.25

Commercial Polish **Back Surface:**

90 **Clear Aperture (%):**

11.25 **Clear Aperture CA (mm):**

Ground **Edges:**

5 **Parallelism (arcmin):**

## Optical Properties

Dielectric **Coating Type:**

Dielectric Mirror (400-750nm) **Coating:**

M4 (typical) **Surface Flatness (P-V):**

400 - 750 **Wavelength Range (nm):**

**BOROFLOAT®** **Substrate:**

0-45 **Angle of Incidence (°):**

**Coating Specification:**  
R<sub>avg</sub> >98% @ 400 - 750nm (0-45°, All Polarizations)  
R<sub>avg</sub> >99% @ 400 - 750nm (0-45°, S-Polarizations)

60-40 **Surface Quality:**

**Damage Threshold, By Design:**   
0.5 J/cm<sup>2</sup> @ 532nm, 20ns, 20Hz

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Enhanced Reflectivity and LDT over Metallic Coatings
- Average Reflectivity >99% from 400 – 750nm
- Designed for all Polarization States at 0 – 45° AOI
- [λ/10](#) Versions Available

TECHSPEC® Broadband Dielectric M4 Mirrors feature a high laser damage threshold of 0.5 J/cm<sup>2</sup> @ 532nm, 20ns pulse, at 20Hz as well as a >99% reflection from 400 – 750nm across all polarization states. Constructed from highly durable BOROFLOAT® substrates, these mirrors feature outstanding thermal and high chemical durability making them ideal for high temperature and harsh environment applications. TECHSPEC® Broadband Dielectric M4 Mirrors are available in a variety of diameters from 12.5 - 50mm. A low-cost alternative to our precision polished [TECHSPEC Broadband Dielectric λ/10 Mirrors](#), these mirrors are ideal for spectroscopy, microscopy, and general laboratory use such as beam steering or reflection applications utilizing multiple laser sources.

**Note:** Surface Flatness is measured pre-coating and deviations may appear after the coating has been applied. For applications where surface flatness is critical it is recommended to use the [TECHSPEC® Broadband Dielectric λ/10 Mirrors](#).