

TECHSPEC<sup>®</sup> 12.5mm Dia. x 17.5mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#49-952-INK** [CONTACT US](#)

☐ [Other Coating Options](#)

-

1

+

€108<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €108,00 each                  |
| Qty 6-25       | €86,00 each                   |
| Qty 26-49      | €81,50 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General


|                                                                                                                                              |                                             |
|----------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------|
| Achromatic Lens                                                                                                                              | Type:                                       |
| Physical & Mechanical Properties                                                                                                             |                                             |
| 12.50 ±0.025                                                                                                                                 | Diameter (mm):                              |
| 11.50                                                                                                                                        | Clear Aperture CA (mm):                     |
| <1                                                                                                                                           | Centering (arcmin):                         |
| 7.30 ±0.10                                                                                                                                   | Center Thickness CT (mm):                   |
| 5.80 ±0.05                                                                                                                                   | Center Thickness CT 1 (mm):                 |
| 1.50 ±0.05                                                                                                                                   | Center Thickness CT 2 (mm):                 |
| 5.08                                                                                                                                         | Edge Thickness ET (mm):                     |
| Protective as needed                                                                                                                         | Bevel:                                      |
| Optical Properties                                                                                                                           |                                             |
| 17.50                                                                                                                                        | Effective Focal Length EFL (mm):            |
| ±1                                                                                                                                           | Focal Length Tolerance (%):                 |
| 13.59                                                                                                                                        | Back Focal Length BFL (mm):                 |
| 587.6                                                                                                                                        | Focal Length Specification Wavelength (nm): |
| 12.20                                                                                                                                        | Radius R <sub>1</sub> (mm):                 |
| -9.82                                                                                                                                        | Radius R <sub>2</sub> (mm):                 |
| -39.19                                                                                                                                       | Radius R <sub>3</sub> (mm):                 |
| N-BAF10 / N-SF57                                                                                                                             | Substrate: □                                |
| 40-20                                                                                                                                        | Surface Quality:                            |
| 1.4                                                                                                                                          | f/#:                                        |
| 0.36                                                                                                                                         | Numerical Aperture NA:                      |
| VIS-NIR (400-1000nm)                                                                                                                         | Coating:                                    |
| Coating Specification:<br>R <sub>abs</sub> ≤0.25% @ 880nm<br>R <sub>avg</sub> ≤1.25% @ 400 - 870nm<br>R <sub>avg</sub> ≤1.25% @ 890 - 1000nm |                                             |
| 1.5λ                                                                                                                                         | Power (P-V) @ 632.8nm:                      |
| λ/4                                                                                                                                          | Irregularity (P-V) @ 632.8nm:               |
| 400 - 1000                                                                                                                                   | Wavelength Range (nm):                      |
| Regulatory Compliance                                                                                                                        |                                             |
| Compliant                                                                                                                                    | RoHS 2015:                                  |
| Compliant                                                                                                                                    | REACH 201:                                  |
| View                                                                                                                                         | Certificate of Conformance:                 |

## PRODUCT DETAILS

- Designed for 0° Angle of Incidence
- Less Than 0.25% Reflectance Per Surface @ 880nm
- **MgF<sub>2</sub>** and **VIS 0°** Coated Achromats Also Available

TECHSPEC® VIS-NIR Coated Achromatic Lenses consist of two optical components cemented together to form an achromatic doublet. The doublet is computer optimized to correct for on-axis spherical and chromatic aberrations. TECHSPEC® VIS-NIR Coated Achromatic Lenses have visible/near-infrared broadband anti-reflection coating, which is specially optimized to yield maximum transmission (>99%) in the near-infrared. The achromatic lenses reduce reflection to less than 0.25 percent per surface at 880nm. **Magnesium Fluoride** coated and **VIS 0°** coated achromats are also available.

## TECHNICAL INFORMATION



## COATING CURVES

## CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## COMPATIBLE MOUNTS