

TECHSPEC[®] 12.7mm Dia., 715 - 980nm, 90R:10T, Ultrafast Beamsplitter



TECHSPEC[®] Ultrafast Beamsplitters

Stock **#13-829** 20+ In Stock

-

1

+

€250⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€250,00 each
Qty 5-9	€222,00 each
Qty 10-19	€196,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads


General	
Ultrafast Non-Polarizing Beamsplitter	Type:
Physical & Mechanical Properties	
3.00 ±0.10	Thickness (mm):
	Diameter (mm):

12.70 +0.00/-0.10	
80	Clear Aperture (%):
<10	Parallelism (arcsec):
Optical Properties	
Fused Silica (Corning 7980)	Substrate: □
10-5	Surface Quality:
45	Angle of Incidence (°):
715 - 980	Wavelength Range (nm):
90/10	Reflection/Transmission Ratio (R/T):
Coating Specification: Surface 1: R _{avg} = 90±3% @ 715 - 980nm R _p = 83±3% @ 715 - 980nm R _s = 97±3% @ 715 - 980nm Surface 2: R _s <2% @ 650 - 1100nm R _p <1.5% @ 650 - 1100nm	
GDD Specification: Transmission: ±65 fs ² @ 715 - 980nm Reflectivity: ±75 fs ² @ 715 - 980nm	
λ/8 @ 632.8nm	Transmitted Wavefront Distortion:
<λ/3 @ 632.8nm	Reflected Wavefront Distortion:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Designs for Ti:sapphire and Yb:doped Fiber Lasers
 - 90:10, 70:30, and 50:50 (R:T) Split Ratios
 - Controlled Reflection and Transmission GDD
- TECHSPEC® Ultrafast Beamsplitters are designed for use with femtosecond pulsed Ti:sapphire and Yb:doped fiber lasers. Their front surface features a 90:10, 70:30, or 50:50 (R:T) non-polarizing beamsplitter coating while their back surface features an anti-reflective coating to minimize losses due to reflection. Each coating has controlled dispersion to allow for predictable group delay dispersion (GDD) of the transmitted or reflected pulses. TECHSPEC Ultrafast Beamsplitters are available in standard imperial sizes for easy integration into optical systems. Please [contact us](#) if your application requires an Ultrafast Beamsplitter with a custom size or coating specifications.
- Note:** The arrow on the edge of these optics points towards the beamsplitter coating.

Technical Information



Compatible Mounts