

[See all 16 Products in Family](#)

**TECHSPEC® 12mm Dia. x 9mm FL, VIS Coated, Hybrid Asphere**



TECHSPEC® Plastic Hybrid Aspheric Lenses

Stock #21-227 **20+ In Stock**

⊖ 1 ⊕ €112.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-24	€112,00 each
Qty 25-99	€89,00 each
Qty 100-249	€66,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Aspheric Lens **Type:**

**Physical & Mechanical Properties**

12.00 ±0.15 **Diameter (mm):**

**Centering (arcmin):**

±3	
10.00	Clear Aperture CA (mm):
2.51	Edge Thickness ET (mm):
5.60	Center Thickness CT (mm):
Protective as needed	Bevel:
Convex	Shape of Back Surface:

## Optical Properties

9.00 @ 587.6nm	Effective Focal Length EFL (mm):
0.67	Numerical Aperture NA:
5.57	Back Focal Length BFL (mm):
K22R	Substrate: <input type="checkbox"/>
587.6	Aspheric Design Wavelength (nm):
BBAR (425-675nm)	Coating:
R <sub>avg</sub> <0.7% @ 425 - 675nm	Coating Specification:
80-50	Surface Quality:
0.75	f#:
48.3	Radius R <sub>2</sub> (mm):
425 - 675	Wavelength Range (nm):
Infinite	Conjugate Distance:
587.60	Focal Length Specification Wavelength (nm):

## Environmental & Durability Factors

-30 to +70	Operating Temperature (°C):
------------	-----------------------------

## Regulatory Compliance

<a href="#">Compliant</a>	RoHS 2015:
<a href="#">View</a>	Certificate of Conformance:
<a href="#">Compliant</a>	Reach 250:

## Product Details

- Color-Corrected Plastic Aspheres
- Diffractive Surface Minimizes Chromatic Aberration
- Low-Cost, Molded Design

TECHSPEC® Plastic Hybrid Aspheric Lenses are molded aspheric lenses with diffraction-limited designs that eliminate chromatic aberrations caused by broadband light sources. These hybrid aspheric lenses are ideal for imaging or ophthalmic applications, or for use with tunable lasers or broadband or multispectral illumination sources. The [aspheric lens](#) eliminates spherical aberration, while the diffractive surface features a negative optical dispersion to yield excellent color correction.

TECHSPEC Plastic Hybrid Aspheric Lenses are similar in performance, but offer several advantages to our [TECHSPEC Aspherized Achromatic Lenses](#). Hybrid aspheric lenses feature all-plastic, monolithic designs that are much lighter than comparable aspherized achromatic lenses. These optical lenses are also available in higher numerical apertures. However, plastic hybrid aspheric lenses are limited by the inherent diffraction efficiency of the aspheric surface, yielding lower overall transmission than comparable aspherized achromatic lenses.

These lenses won the 2011 Prism Award for Optics and Optical Components.

## Technical Information

