

[See all 1 Products in Family](#)

## 13.5nm, 25.4mm Dia, 5° AOI, EUV Spherical Mirror



TECHSPEC® Extreme Ultraviolet (EUV) Spherical Mirrors

Stock #11-730 **20+ In Stock**

- 1 + €4.310<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€4.310,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Spherical Mirror **Type:**

#### Physical & Mechanical Properties

25.40 +0.00/-0.13 **Diameter (mm):**

6.35 ±0.25 **Thickness (mm):**

**Surface Roughness (□):**

<3 RMS

## Optical Properties

Metal/Semiconductor **Coating Type:**

Mb/Si Multilayer **Coating:**  
Top Layer: Silicon

M10 @ 632.8nm **Surface Flatness (P-V):**

13.5 **Design Wavelength DWL (nm):**

250.00 **Effective Focal Length EFL (mm):**

[Fused Silica](#) (Corning 7980) **Substrate:**

5 **Angle of Incidence (°):**

R<sub>abs</sub> >60% @ 13.5nm **Coating Specification:**

500.00 **Radius R<sub>1</sub> (mm):**

500.00 **Radius of Curvature (mm):**

0.50 **Full Width-Half Max FWHM (nm):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Mb/Si Multilayer Coating on Super-Polished Substrates
- Maximum Achievable Reflection at 13.5nm
- Designed for EUV Beam Focusing Applications
- Narrow Pass Band for HHG Applications

Extreme Ultraviolet (EUV) Spherical Mirrors feature a multilayer Mb/Si coating providing greater than 60% reflection at 13.5nm. They are designed for a 5° angle of incidence and intended for focusing unpolarized EUV laser sources. A surface roughness of less than 3  $\square$  RMS minimizes scatter. This is essential for EUV wavelengths which experience more scattering than longer wavelengths. EUV Spherical Mirrors have a very narrow pass band of approximately 0.5nm, ensuring that only the 13.5nm harmonic of interest is reflected in high harmonic generation (HHG) applications. [Typical applications](#) for EUV spherical mirrors include Coherent Diffractive Imaging (CDI), EUV imaging, and EUV nanomachining.

**Note:** Test data from each mirror's production run sample included.