

## TECHSPEC® 15.0mm Dia. x 30.0mm FL, NIR II, Inked, Plano-Convex Lens



Stock #67-519-INK [CONTACT US](#)

[Other Coating Options](#)

⊖ 1 ⊕ **€51,50**

ADD TO CART

Qty 1-9

€51,50

Qty 10+

€46,25

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Diameter (mm):**  
15.00 ±0.025

**Effective Focal Length EFL (mm):**

30.00 @ 587.6nm

**Back Focal Length BFL (mm):**  
27.90

**Coating:**  
NIR II (750-1550nm)

**Coating Specification:**  
R<sub>abs</sub> ≤ 1.5% @ 750 - 800nm  
R<sub>abs</sub> ≤ 1.0% @ 800 - 1550nm  
R<sub>avg</sub> ≤ 0.7% @ 750 - 1550nm

**Substrate:**   
[N-BK7](#)

**Surface Quality:**  
40-20

**Power (P-V) @ 632.8nm:**  
1.5λ

**Irregularity (P-V) @ 632.8nm:**  
λ/4

**Focal Length Tolerance (%):**  
±1

**Centering (arcmin):**  
<1

**Center Thickness CT (mm):**  
3.18 ± 0.10

**Edge Thickness ET (mm):**  
1.25

**Radius R<sub>1</sub> (mm):**  
15.52

**Clear Aperture CA (mm):**  
14

**f#:**  
2

**Numerical Aperture NA:**  
0.25

**Type:**  
Plano-Convex Lens

**Bevel:**  
Protective bevel as needed

**Wavelength Range (nm):**  
750 - 1550

**Damage Threshold, By Design:**   
8 J/cm<sup>2</sup> @ 1064nm, 10ns

## Regulatory Compliance

**RoHS:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

---