

150mm FL, 1064nm Edmund Optics® F-Theta Lens



Stock #15-180 CLEARANCE 1 In Stock

€675^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€675,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

F-Theta Lens Type:

Physical & Mechanical Properties

87 Maximum Diameter (mm):

189.5 Flange Distance (mm):

12 Input Beam Diameter, 1/e² (mm):

54.3 Maximum Length (mm):

Optical Properties

152.20 Focal Length FL (mm):

±22.62 Scan Angle (°):

86.0 x 86.0 Scan Field (mm):

Not Specified Telecentricity (°):

≥95 Transmission (%):

171.2 Working Distance (mm):

1064 Design Wavelength DWL (nm):

1064 Wavelength Range (nm):

26 Focus Size Diameter, 1/e² (μm):

Threading & Mounting

M85 x 1.0 Mounting Threads:

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Ideal for Laser Scanning Applications
- Diffraction Limited Across the Scan Field with Low Wavefront Error
- Long Working Distances and Large Scan Areas
- [Galvanometers](#), [Beam Expanders](#), and [Laser Sources](#) Also Available

Edmund Optics® F-Theta Lenses are designed to provide flat fields at the image plane of scanning systems and are used in conjunction with [galvanometers](#), [beam expanders](#), and [laser sources](#). These F-Theta Lenses feature compact form factors, offer a wide range of focal lengths up to 273mm, and large scan fields up to 164mm (X) x 164mm (Y). Optimized for common fiber laser sources and Nd:YAG fundamental or second harmonic, these lenses are available in design wavelengths of 532nm and 1064nm with common mounting threads for easy integration into galvo systems. Edmund Optics® F-Theta Lenses are a cost-effective solution for laser scanning and laser processing applications including laser marking, engraving, cutting, drilling, and 3D modeling.