

[See all 75 Products in Family](#)

**TECHSPEC® 18mm Dia., 0.60 NA, 900-1700nm Coated, NIR Aspheric Lens**



TECHSPEC® Near-Infrared (NIR) Aspheric Lenses

Stock **#16-294** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ €269.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€269,00 each
Qty 6-10	€242,00 each
Qty 11-25	€226,00 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Aspheric Lens **Type:**

**Physical & Mechanical Properties**

18.00 +0.00/-0.10 **Diameter (mm):**

<3	Centering (arcmin):
16.2	Clear Aperture CA (mm):
2.55	Edge Thickness ET (mm):
6.20 ±0.10	Center Thickness CT (mm):
Protective as needed	Bevel:
Plano	Shape of Back Surface:

## Optical Properties

15.00 @ 780nm	Effective Focal Length EFL (mm):
0.60	Numerical Aperture NA:
11.51	Back Focal Length BFL (mm):
<a href="#">S-LAH64</a>	Substrate: <input type="checkbox"/>

780	Aspheric Design Wavelength (nm):
1.2λ	Asphere Figure Error, RMS @ 632.8nm:
SWIR+ (900-1700nm)	Coating:
R <sub>avg</sub> < 0.5% @ 900 - 1700nm @ 0° ±30° AOI R <sub>abs</sub> < 1% @ 900 - 1700nm @ 0° ±30° AOI	Coating Specification:

40-20	Surface Quality:
0.83	f#:

47.37	Abbe Number (v <sub>d</sub> ):
1.788	Index of Refraction (n <sub>d</sub> ):

900 - 1700	Wavelength Range (nm):
Infinite	Conjugate Distance:

66.67	Power (diopters):
-------	-------------------

## Material Properties

6.1	Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C):
-----	--

## Regulatory Compliance

<a href="#">Compliant</a>	RoHS 2015:
<a href="#">Compliant</a>	Reach 223:

<a href="#">View</a>	Certificate of Conformance:
----------------------	-----------------------------

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Optimized for Applications in the NIR
- Uncoated or AR coated versions available

- **Multiple Design Wavelengths Available**

TECHSPEC® Near-Infrared (NIR) Aspheric Lenses are optimized to eliminate spherical aberration in the near-infrared. Manufactured from S-LAH64 or N-BK7 substrates and polished through a computer numerical controlled (CNC) process, these aspheric lenses achieve high precision performance across the NIR spectrum. These NIR aspheric lenses include uncoated substrates designed at 780nm with coating options at 350-700nm, 600-1050nm, or 900-1700nm. TECHSPEC® Near-Infrared (NIR) Aspheric Lenses are available with low numerical aperture designs for applications that require beam shape to be maintained as well as high numerical aperture designs for light-gathering applications. For custom designed CNC polished aspheric lenses, please contact us.

## Compatible Mounts

---

;