

**TECHSPEC® 20mm VIS, Lateral Displacement Non-Polarized Beamsplitter**



Lateral Displacement Beamsplitters

Stock **#47-189** **20+ In Stock**

⊖ 1 ⊕ €800<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€800,00 each
Qty 6-25	€635,00 each
Qty 26-99	€590,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Non-Polarizing Beamsplitter

Type:

Non-Polarizing

Type of Optics:

**Physical & Mechanical Properties**

Clear Aperture (%):

80.00

**Construction:**

Prism

**Dimensional Tolerance (mm):**

±0.1

**Parallelism (arcmin):**

<2

**Optical Properties**

**Angle Tolerance (arcsec):**

±5

**Beam Separation (mm):**

20.00

**Coating Specification:**

R<sub>avg</sub> <0.5% @ 430 - 670nm

**Extinction Ratio:**

|T<sub>p</sub> - T<sub>s</sub>| <6%

**P-Polarization Transmission (%):**

45.00

**Reflection/Transmission Tolerance (%):**

±10

**S-Polarization Reflection (%):**

45.00

**Substrate:**

**N-BK7**

**Surface Flatness (P-V):**

λ/8

**Surface Quality:**

40-20

**Wavelength Range (nm):**

430 - 670

**Regulatory Compliance**

**Certificate of Conformance:**


[View](#)

## Product Details

- Visible and NIR Coating Options Offered
- Simplifies Benchtop Layout
- Split Incident Beam into Two Displaced Parallel Beams

TECHSPEC® Lateral Displacement Beamsplitters output two parallel beams separated by a fixed distance. The beamsplitters consist of a precision **rhomboid prism** cemented to a **λ/8 right angle prism**. The high tolerance design ensures the exiting beams are parallel to within 2 arcmin. TECHSPEC® Lateral Displacement Beamsplitters' entrance and exit faces feature a multi-layer anti-reflection (AR) coating for increased efficiency. Polarizing and non-polarizing coatings are available for these beamsplitters.

## Technical Information



Size (A)	10mm	20mm
Beam Separation	10mm	20mm



;