

20mW 320nm OBIS XT

See More by [Coherent®](#)



Stock #75-316 NEW CONTACT US

-
1
+
€29.960⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€29.960,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Warm-Up Time (minutes):	<5
Manufacturer:	Coherent®
Type of Laser:	Diode Pumped Solid State
Laser Class - CDRH:	IIIb
Model Number:	1371110

Physical & Mechanical Properties

Dimensions (mm):
125.0 x 70.0 x 36.5

Weight (g):
450

Pointing Stability ($\mu\text{rad}/^\circ\text{C}$):
<5

Pointing Stability (μrad):
<30

Optical Properties

Polarization:
100:1

Spatial Mode:
 TEM_{00}

Wavelength (nm):
319.80

Mode Quality, M^2 :
 ≤ 1.1

Beam Diameter Tolerance (mm):
 ± 0.05

Beam Diameter (mm):
0.7

Beam Divergence (mrad):
Full-Angle: <0.7

Color:
UV

Electrical

Output Power (mW):
20

RMS Noise:
 $\leq 0.25\%$ (20Hz to 20MHz)

Hardware & Interface Connectivity

Output Type:
Free Space

Environmental & Durability Factors

Operating Temperature ($^\circ\text{C}$):
+10 to +35

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- Compact, Thermally Efficient Design for Ease of Life Science System Integration
- 320, 349, and 640nm Wavelength Options Available
- Integrated Controller with RS-232, RS-485, and USB Interfaces

Coherent OBIS XT Laser Systems offer an advanced extension of the [OBIS LS/LX](#), delivering powerful performance across ultraviolet and visible wavelengths. These lasers are available in UV wavelengths of 320 and 349nm, with output power options ranging from 20 to 150mW, and a higher-power 640nm wavelength option with output powers of 400 or 500mW. Flexible communication interfaces, including RS-232, RS-485, and USB, allow for seamless integration and real-time control in complex applications. Coherent OBIS XT Laser Systems are designed to simplify system integration, utilizing their compact form factor, integrated controller, as well as a low thermal output. This reduces the need for external cooling and streamlines OEM and end-user implementation. OBIS XT lasers are ideal for a wide range of applications, including life sciences, biomedical, flow cytometry, DNA Sequencing, and fluorescence microscopy.