

25.4mm Clear Aperture 40R/40T, Pellicle Beamsplitter



Pellicle Beamsplitters

Stock **#39-479** **2 In Stock**

-

1

+

€311⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	€311,00 each
Qty 11-25	€265,00 each
Qty 26+	€229,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Pellicle Beamsplitter

Type:

Physical & Mechanical Properties

25.4

Clear Aperture CA (mm):

Construction:

Pellicle	
34.90	Diameter (mm):
Black Anodized Aluminum	Housing:
2 +0.3/-0.0	Thickness (µm):

Optical Properties

		Coating:
Metal/Dielectric		
		Coating Specification:
40/40 @ 400 - 700nm		
		Index of Refraction (n _d):
1.5		
		Reflection/Transmission Ratio (R/T):
40/40 ±5%		
		Substrate: □
Nitrocellulose		
		Surface Quality:
40-20		
		Wavelength Range (nm):
400 - 700		

Threading & Mounting

		Mount Thickness (mm):
4.76		
		Mounting Threads:
2-56		

Regulatory Compliance

		RoHS 2015:
Compliant		
		Certificate of Conformance:
View		
		REACH 241:
Compliant		


Product Details

- No Ghost Images from Second Surface Reflections
- No Chromatic Aberration with Converging Beams
- No Change in Optical Path Length
- [Pellicle Beamsplitters for the Infrared \(IR\)](#) Also Available

Pellicle Beamsplitters are very thin nitrocellulose membranes bonded to lapped aluminum frames. They feature no ghost images from second surface reflections. To ease system integration, these beamsplitters offer mounting holes on the underside of the frame. Pellicle Beamsplitters are resistant to mechanical shock or climate variations but must be protected from dust and spray to avoid damage to the pellicle membrane. Please note, environments with a high level of humidity (>55%) can cause a temporary loss of tension in the pellicle membrane. The membrane will revert to normal tension if humidity is lowered.

Note: Extra care must be taken when handling.

Technical Information





Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Compatible Mounts