

[See all 3 Products in Family](#)

25.4mm Dia., 650 - 1350nm, Complementary Chirped Mirror Pair

See More by [UltraFast Innovations \(UFI\)](#)



UltraFast Innovations (UFI) Ultra-Broadband Complementary Chirped Mirror Pairs

Stock #14-674 **4 In Stock**

- 1 + €1.952⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€1.952,00 each
Qty 5-9	€1.373,00 each
Qty 10+	€1.226,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Sold as a Set of 2

Note:

PC147

Model Number:

Physical & Mechanical Properties

10 ±5	Wedge Angle (arcmin):
80	Clear Aperture (%):
Commercial Polish	Back Surface:
25.40 +0.00/-0.10	Diameter (mm):
6.35 ±0.20	Thickness (mm):
Protective as needed	Bevel:

Optical Properties

R _{avg} >99% @ 650 - 1350nm (5° AOI, p-polarization)	Coating Specification:
-60fs ² @ 650 - 1350nm (5° AOI, p-polarization)	GDD Specification:
650 - 1350	Wavelength Range (nm):
λ10	Irregularity (P-V) @ 632.8nm:
Dielectric	Coating Type:
Complementary Chirped Pair (650-1350nm)	Coating:
5	Angle of Incidence (°):
Fused Silica (Corning 7980)	Substrate: <input type="checkbox"/>
0.2 J/cm ² @ 800nm, 50fs	Damage Threshold, By Design: <input type="checkbox"/>

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details


- Ideal for Chirped-Pulse Amplifier Systems and Ultra-Broadband Laser Oscillators
- Ultra-Broadband Design Supports Dispersion Compensation
- Negative GDD as Low as -60fs² and High Reflectivity (>99%) at 600 – 950nm or 650 – 1350nm

UltraFast Innovations (UFI) Ultra-Broadband Complementary Chirped Mirror Pairs are designed to provide dispersion compensation for ultrafast pulses. The matched mirrors feature out-of-phase group delay dispersion (GDD) oscillations leading to a near-constant GDD performance with minimal oscillations. The broadband coating design covers the most common ultrafast laser lines, including Ti:sapphire and Yb:doped fiber, providing negative GDDs as low as -60fs² and average reflectance of >99% (p-polarization) at 600 – 950nm or 650 – 1350nm. The narrow angles of incidence (AOI) allows many reflections of the ultrafast pulse to effectively compensate for dispersion effects. UFI Ultra-Broadband Complementary Chirped Mirror Pairs are ideal for dispersion compensation in ultrafast laser applications, including chirped-pulse amplifier systems and ultra-broadband laser oscillators. Please contact us for custom mirror pairs with different geometries, bandwidths, or spectral specifications.

Note: Complementary Chirped Mirror Pairs are sold in pairs.

Technical Information

650 - 1350nm, Complementary Chirped Mirror Pair Coating Reflectivity/GDD Performance



Compatible Mounts

;